

Technical Analyse of CUTBACK BITUMEN RAPID

Specification	Min	Max	Method
Kinematic Viscosity at 60° C mm ² /s	70	140	ASTM D2170
Flash Point (Tag Open-Cup),°C	38	-	ASTM D3143
Distillate Test: Distillate, Volume Percent of Total Distillate to 360° C			
To 225° C	50	-	ASTM D402
To 260° C	70	60	ASTM D402
To 316° C	85	90	ASTM D402
Residue from distillation to 360° C, percent volume by difference	55	-	ASTM D402
Tests on Residue from Distillation			
Viscosity at 60 °C	30	120	ASTM D2170
Penetration at 25 °C	80	120	ASTM D5
Ductility at 25 °C	100	-	ASTM D113
Solubility in trichloroethylene, %	99	-	ASTM D2042
Water, %	-	0.2	ASTM D95